


### a|Adapter


Connect BeamTuning elements conveniently to any optical set-up with matching adapters. Intra-system a|Adapters allow to use a|BeamExpander in both functional directions, to expand or reduce the beam diameter. The a|Adapter tilt can even be inclined in different directions and compensate for application-related tilts within the beam path. The cross-system a|Adapters guarantee a high level of compatibility with other optical systems (e.g. Qioptiq, OWIS) – without additional adjustment.

#### Technical Dimensions:


**C-MOUNT MALE**




**C-MOUNT FEMALE**




**1.2" CIRCUMFERENCE (DUAL USE)**




**SM1 MALE**




**SM1 FEMALE**



**TILT**



**INTRA-SYSTEM**



Product Code	Adapter Type	Thread Type	Length [mm]
UAM25-28-C-MIO	C-Mount male	male/female	12.3
UAM25-28-C-MII	C-Mount female	female/female	10.3
UAM25-28-SM1-MIO	SM1 male	male/female	12.3
UAM25-28-SM1-MII	SM1 female	female/female	10.3
UAM25-28-1.2in-MII	1.2" circumference	female/female	12.1
UAM25-28-tilt-MIO	Tilt	female/male	27.5
UAM25-28-A-MOO	Intra-System	male/male	12.2



asphericon GmbH  
Stockholmer Str. 9 | 07747 Jena  
Germany

+49 (0) 3641 - 3100 560  
+49 (0) 3641 - 3100 561

asphericon, Inc.  
2601 Cattlemen Road, Suite 301  
Sarasota, FL 34232 | USA

+1 - 941 - 564 0890

asphericon s.r.o.  
Milířská 449 | Jeřmanice 463 12  
Czech Republic

+420 488 100 300

sales@asphericon.com

www.asphericon.com