

C COATING


Measured curve for StockOptics & BeamTuning

Material: Fused Silica

Wavelength: 1000 - 1600 nm

Date: 02.05.2019

Measuring Instrument: PerkinElmer UV WinLab Data Processor and Viewer Version 1.00.00



— 1 010232-203-03A Run 2312/114/15 AOI 8°
 — 2 010232-203-03A Run 2313/114/15 AOI 8°

asphericon GmbH

Stockholmer Str. 9 | 07747 Jena
 Germany



+49 (0) 3641 - 3100 560



+49 (0) 3641 - 3100 561

asphericon, Inc.

5500 Bee Ridge Road, Suite 104
 Sarasota, FL 34233 | USA



+1 - 941 - 564 0890



sales@asphericon.com



www.asphericon.com

asphericon, s.r.o.

Miliřská 449 | Jeřmanice 463 12
 Czech Republic



+420 488 100 300